



NEOCLEAN

Liquid detergent formulated for interoperational degreasing of machined metal parts, by soaking or by spraying.

COMPATIBILITY:

- Titanium
- Stainless steel
- Copper

INGREDIENTS:

- Surfactants, phosphates
- Solvating agents, anti-corrosion agents

PHYSICAL AND CHEMICAL DATA:

- pH concentrated: 8.4
- pH (1%): 7.4
- Density: 1.009
- Surface tension: 27.7 mN/m

INSTRUCTIONS FOR USE:

Optimum use conditions may be affected by the quality of the water used in the baths, as well as the type and quantity of contaminants.

- Concentration for dipping: 5 to 10%
- Concentration for spraying: 3%
- Temperature: 20 to 60°C (68 to 140°F)
- Time: 3 to 5 min.

FOR USE IN THE NGL FD60 DEGREASING FOUNTAIN:

Degreasing fountain intended for several types of industries: watchmaking, medical, electronics, micromechanics and aeronautics...

It replaces traditional solutions that use solvents, oils or alcohols, which are harmful to health and the environment.

BENEFITS:

- Substitute for kerosene and solvents
- Water based solution
- Reduced operating costs
- Improved safety/environmentally safe
- Recycling of the degreasing solution
- Improved cleanliness and organisation of workshops
- Mobile equipment

BENEFITS:

- Greater biodegradability, helps to preserve the environment
- Non-toxic to operators
- Efficient at room temperature
- An alternative to kerosene, for use with the NGL FD60 degreasing fountain
- Contains no VOCs

STORAGE CONDITIONS:

- Keep the recipient hermetically sealed between 5°C and 40°C (41°F and 104°F) in a dry place.
- Always keep in packaging made from the same material as the original packaging.



If you have any questions, please contact our Application Centre on: +41 22 365 46 66

